



VREL® VARIABLE PRESSURE REDUCING ELEMENT

U.S. Patent No. RF37.153

New Heavy-Duty Speed Handle Substantially Reduces Turning Effort

Features

- Ergonomic speed handle substantially reduces turning effort
- No valve/regulator erosion or wire drawing
- Fine flow control
- Fully retractable rods assure easy online purging
- Extended-body design eliminates possibility of bent tubes
- Flows from 150 milliliters per minute up to 4 liters per minute at pressure drops up to 5000 psig (345 barg)

Disponibile versione 538 bar



Description

Chemical analysis of water and steam samples in modern power generation plants requires precise control of flow and pressure. High pressure reduction presents sampling problems for the system designer. The Sentry $VREL^{\circledR}$ is a valve specifically designed to solve unique high pressure sampling problems.

Industry Standard

The patented VREL[®] is the industry standard for samples greater than 500 psig (34.5 barg) according to the Annual Book of ASTM Standards, ASTM Designation D3370.

The adjustable rod-in-tube type design allows for variable pressure drop and flow control. The VREL $^{\mathbb{R}}$ is also cleanable in place. Both of these design factors provide the advantages needed for consistent sample conditioning.

Adjustable


When source pressures change, such as at startup and shutdown, the VREL[®] can be easily adjusted to allow continuous monitoring under all pressure conditions.

Cleanable in Place

Since corrosion products, scale, and other foreign matter often find their way into sample lines, plugging of the pressure reduction valve is common. This is particularly true of Labrynth-type (Drag) valves, and diaphragm-operated high pressure regulators. If these valves plug, the sample line must be shut down while the valve is removed for cleaning or replacement. If the Sentry VREL® plugs with solids, the rods can be fully retracted and the obstruction blown free without disconnecting any lines. The analyzer can be returned to service in minutes by operating personnel.

Rometec srl - www.rometec.it - info@rometec.it - Rometec srl - www.rometec.it - info@rometec.it

Rometec srl - www.rometec.it - info@rometec.it - Rometec srl - www.rometec.it - info@rometec.it



CONSTRUCTION & OPERATION

The VREL[®] consists of two stainless steel tubes joined to a large tube or barrel. A tapered rod assembly is provided and inserted into precision holes in the barrel. The high pressure fluid enters, flows past one rod, turns and flows past the other rod, then out. Pressure drop is a function of the length of the rods inserted into the barrel.

The pressure is reduced smoothly under laminar flow conditions, minimizing dissociation of any components through discontinuous pressure drops. The rod position is controlled externally by turning the knob, and can be adjusted while the sample is flowing. If blockage occurs, the rods can be retracted so that system pressure can blow the solid matter through.

SPECIFICATIONS

Wetted Materials	316 stainless steel
Weight	4 lbs. / 2 kg
Ratings	5000 psig at 300°F / 345 barg at 149°C
Standard end connection	

Optional end connections are listed below.

NOTE: The VREL® is not a shut off valve. The minimum flow which can be obtained is approximately 150 cc/min.

PART NUMBERS

1/4" Plain Ends	7-00744A	Spare Parts:	
1/4" Socket Weld	7-00747A	Handle and Rod Kit	6-02302E
3/8" Socket Weld	7-00748A	Seal Kit	6-02302C
1/2" Socket Weld	7-00749A		
1/4" 37° Fitting	7-00745A		
3/8" 37° Fitting	7-00746A		



SENTRY EQUIPMENT CORP

856 East Armour Road PO Box 127 Oconomowoc, WI 53066 USA Phone: 262-567-7256 Fax: 262-567-4523

E-mail:

sales@sentry-equip.com

Website:

www.sentry-equip.com

For further information, contact:

Rometec srl

Via Alessandro Minuziano, 87 - 89 00128 - Roma Tel 06-5061635 Fax 065061542 P.Iva 0412062100

www.rometec.it

Rometec srl - www.rometec.it - info@rometec.it - Rometec srl - www.rometec.it - info@rometec.it